

TZ

XX Number of contacts		X Pitch	X Screw&Clamp	X Color	X Body type	X	X	X	X	X
Solid Block 02 2 contacts 03 3 contacts 24 24 contacts (pitch 3.5&5.0) 12 12 contacts (pitch 7.0&10.0)		2 3.5/.138" 0 5.0/.197" 3 7.0/.276" 1 10.0/.394"	0 "+/-" Combination type W/Brass Machined Clamp 1 "-" Slotted screw W/Brass Machined Clamp	0 Black	0 With pillar & W/O cover 1 With pillar & With cover (Tape reel) 2 W/O pillar & W/O cover (pitch 3.5&7.0) 3 W/O pillar & With cover (Tape reel) (pitch 3.5&7.0)	0000 Standard B000 Tape reel (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy			