

V8

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

X

Body type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ..
24 24 contacts
(pitch 3.81&5.08)
16 16 contacts
(pitch 7.62)

3 3.81/.15"
5 5.08/.20"
0 7.62/.30"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 W/O flange
1 Flange with nut
2 Flange with screw

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy