

T3

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Body type

X

X

X

X

X

02 2 contacts
03 3 contacts
.. ..
24 24 contacts
(pitch 5.0)
12 12 contacts
(pitch 10.0)

0 5.0/.197"
1 10.0/.394"

4 "+/-" Combination type
W/Brass Stamping Clamp
5 "-" Slotted screw
W/Brass Stamping Clamp

0 Black
2 Red
3 Orange
4 Yellow
5 Green
(RAL 6018/T)
6 Blue
8 Grey
9 White
C Green
(RAL 6018/U)

1 Stackable
(180D wire inlet)
3 Stackable
(90D wire inlet)
4 Solid block
(180D wire inlet)
5 Solid block
(90D wire inlet)

0000 Standard
(Steel screw plating Cr⁺⁺)
Any special item by
customer request,
please contact sales
department.

F RoHS compliant
(lead<100ppm)
In copper Alloy
G RoHS compliant
(lead<4%)
In copper Alloy
H RoHS compliant
(lead<1000ppm)
In copper Alloy