

VC

XX
Number of contacts

X
Pitch

X
Body type

X
Color

X
Tail type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ...
16 16 contacts

0 7.62/.30"

0 W/O flange
1 Flange with nut

0 Black
5 Green (RAL 6018/T)
6 Blue (RAL 5015/A)
8 Grey (RAL 7035/D)
C Green (RAL 6018/U)

0 Right angle(two tail type)
1 Vertical(two tail type)
A Vertical(three tail type)
B Right angle(three tail type) (PCB up)
C Right angle(three tail type) (PCB down)

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy