

VP

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Tail type

X

X

X

X

X

End Stackable
02 2 contacts
03 3 contacts
...
12 12 contacts
(pitch 10.16&12.7)

6 10.16/.400"
8 12.7/.500"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp
4 "+/-" Combination type
W/Steel Stamping Clamp
5 "- " Slotted screw
W/Steel Stamping Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

4 Single tail
(solder pin size: 1.0*1.0)
5 Double parallel tail
(solder pitch 5.08,
solder pin size: 1.2*1.2)
7 Double interlace tail
(solder pitch 4.0,
solder pin size: 1.0*0.9)
8 Double parallel tail
(solder pitch 4.0,
solder pin size: 1.0*0.9)

0000 Standard
A000 Monolithic contact
(Steel screw plating Cr*)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy