

VN

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

0

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ...
24 24 contacts

A 2.54mm/.1"

0 "+/-" Combination type screw
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy