

TS

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Body type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ..
24 24 contacts
(pitch 3.5&3.81&5.0&5.08)
16 16 contacts
(pitch 7.5&7.62)

1 3.5/.138"
3 3.81/.15"
5 5.08/.20"
7 5.0/.197"
0 7.62/.30"
A 7.5/.295"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp
2 "+/-" Combination type
W/Zinc Alloy Clamp
3 "- " Slotted screw
W/Zinc Alloy Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

A Hook on entry side
B Hook on back side
C With flange &
Hook on entry side
D With flange &
Hook on back side

0000 Standard
(Steel screw plating Cr")
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy