

VD

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

X

Body type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ...
24 24 contacts

3 3.81/.15"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green (RAL 6018/T)
6 Blue
8 Grey (RAL 7035/D)
C Green (RAL 6018/U)

0 Without flange
2 With flange

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy