

YN

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

X

Tail length

X

X

X

X

X

End Stackable
06 3*2 contacts
09 3*3 contacts
.. ..
72 3*24 contacts
(pitch 5.0/5.08)
36 3*12 contacts
(pitch 10.0/10.16)

0 5.0/.197"
1 10.0/.394"
2 5.08/.20"
3 10.16/.40"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 3.5mm

0000 Standard
(Steel screw plating Cr³)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy