

YP

XX
Number of contacts

X
Pitch

X
Screw & Clamp

X
Color

X
Tail length

X
Special insulator

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ...
24 24 contacts
(pitch 3.5/3.81)
12 12 contacts
(pitch 7.0/7.62)

0 3.5/.138"
1 7.0/.275"
2 3.81/.15"
3 7.62/.30"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)

0 3.7mm

0 Standard
A High type
(only pitch
3.81/7.62)

000 Standard
(Steel screw plating Cr⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy