

YR

XX  
Number of contacts

X  
Pitch

X  
Screw&Clamp

X  
Color

0

X

X

X

X

X

Solid Block  
02 2 contacts  
03 3 contacts  
.. ...  
24 24 contacts

0 5.0/.197"  
2 5.08/.20"

0 "+/-" Combination type  
W/Brass Machined Clamp  
1 "- " Slotted screw  
W/Brass Machined Clamp

0 Black  
5 Green  
(RAL 6018/T)  
6 Blue  
8 Grey  
(RAL 7035/D)  
C Green  
(RAL 6018/U)

0000 Standard  
(Steel screw plating Cr<sup>3+</sup>)  
Any special item by  
customer request,  
please contact sales  
department.

G ROHS compliant  
(lead<4%)  
In copper alloy  
  
H ROHS compliant  
(lead<1000ppm)  
In copper alloy