

YM

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Tail length

X X X X X

End Stackable
04 2*2 contacts
06 2*3 contacts
.. ..
48 2*24 contacts
(pitch 5.0&5.08)
24 2*12 contacts
(pitch 10.0&10.16)

0 5.0/.197"(left)
1 10.0/.394"(left)
2 5.0/.197"(right)
3 10.0/.394"(right)
4 5.08/.20"(left)
5 10.16/.40"(left)
6 5.08/.20"(right)
7 10.16/.40"(right)

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 3.5mm

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy