

YS

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

0

X

X

X

X

X

End Stackable
04 2*2 contacts
06 2*3 contacts
... ..
48 2*24 contacts
(pitch 5.0/5.08)
24 2*12 contacts
(pitch 10.0/10.16)

0 5.0/.197"
1 10.0/.394"
2 5.08/.20"
3 10.16/.40"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy