

YK

XX	X	XX	X	X	X	X	X	X	X
Series No.	Changable code	Number of contacts	Cover&Flange	Screw&Contacts plating	Body logo				
11 Series	1 2 3 4 E	02 03 ... 30 04	3 With flange & W/O cover 0 W/O flange & W/O cover	0 Screw & Contacts plating G/F 1 Screw plating Zinc & Contacts plating G/F 2 Screw plating G/F & Contacts plating Sn 3 Screw plating Zinc & Contacts plating Sn (standard)	0 "@" logo (standard) 1 "ANYTEK" logo	Customer's special requirements "01~99" 00 Standard	G ROHS compliant (lead<4%) In copper alloy H ROHS compliant (lead<1000ppm) In copper alloy		
66 Series 77 Series	1	2*2 2*3 ... 2*15 ... 2*21	1 With flange & With cover 3 With flange & W/O cover						