

YL

XX

Number of contacts

X

Pitch

X

Screw&Clamp

X

Color

X

Body type

X

X

X

X

X

End Stackable
04 2*2 contacts
06 2*3 contacts
.. ..
48 2*24 contacts
(pitch 5.0&5.08)
24 2*12 contacts
(pitch 10.0&10.16)

0 5.0/.197"(left)
1 10.0/.394"(left)
2 5.0/.197"(right)
3 10.0/.394"(right)
4 5.08/0.20"(left)
5 10.16/0.40"(left)
6 5.08/0.20"(right)
7 10.16/0.40"(right)

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)

0 Stackable
1 Solid block
(only pitch 5.08-R)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy