

YT

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

0

X X X X X

End Stackable
08 4*2 contacts
12 4*3 contacts
.. ...
96 4*24 contacts

0 5.0/.197"
2 5.08/.20"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green (RAL 6018/T)
6 Blue
8 Grey (RAL 7035/D)
C Green (RAL 6018/U)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy