

YQ

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Tail length

X
Special insulator

X

X

X

X

Solid Block
04 2*2 contacts
06 2*3 contacts
... ..
48 2*24 contacts
(pitch 3.5/3.81)
24 2*12 contacts
(pitch 7.0/7.62)

0 3.5/.138"(left)
1 7.0/.275"(left)
2 3.5/.138"(right)
3 7.0/.275"(right)
4 3.81/.15"(left)
5 7.62/.30"(left)
6 3.81/.15"(right)
7 7.62/.30"(right)

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)

0 3.7mm

0 Standard
A High type
(only pitch
3.81/7.62)

000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy