






300V 15A 22-14AWG 1.5mm²
Poles: 2&3-24P
Pitch: 5.0mm(.197")

Materials

Housing: PBT (UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel (A3), Zinc Plated
Torque: 0.4N.m

设计/Designed by	绘图/Drawing by	审核/checked by	批准/Approved by	备注/Remarks	
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD	图名/Title	文件编号/File No.		X. ±0.2	X. ±2°
	XY301R-A			.X ±0.1	.X° ±1°
	页次/Sheet			.00X ±0.05	.00° ±0.5°
	备注/Remark			.00X ±0.01	
				单位/Unit: mm	