

SPG6-B-10C

Surge protector, 6 sockets, 10 ft

PURE POWER

- Protects valuable equipment from harmful power surges
- Suitable for high power consumption devices
- Overload protection



Features

- GS approved surge protector with German type AC sockets
- Power surge and over-voltage suppression: protects computers, other office equipment and home appliances from harmful power surges and spikes
- 16 A automatic circuit breaker
- High quality, flame retardant plastic case
- Mounting holes
- VDE-approved power cord with German plug
- Power rocker switch with indicator light

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

30
0.061
22.4
98x45x390 mm
520x300x390 mm
CN
8716309068673
8536301000

Specifications

Rating: up to 250 V AC (50Hz), 16 A, safety class IP20
Maximum surge voltage 4,500 V, maximum spike current 4,500 A

Sockets: 6 pcs, German type
Cable length: 3 m
Color: grey

Certificates

