

SPG6-B-6C

Surge protector, 6 sockets, 6 ft

PURE POWER

- Protects valuable equipment from harmful power surges
- Suitable for high power consumption devices



Features

- GS approved surge protector with German type AC sockets
- Power surge and over-voltage suppression: protects computers, other office equipment and home appliances from harmful power surges and spikes
- 16 A automatic circuit breaker
- High quality, flame retardant plastic case
- Mounting holes
- VDE-approved power cord with German plug
- Power rocker switch with indicator light

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

30
0.054
17
395x80x50 mm
420x405x315 mm
CN
8716309068666
8536301000

Specifications

Rating: up to 250 V AC, 16 A, safety class IP20
Maximum surge voltage 4,500 V, maximum spike current 4,500 A

Sockets: 6 pcs, German type
Cable length: 1.8 m
Color: grey

Certificates

