

TA-UC-2A2C-PD100-01-BK

4-port 100 W GaN USB PowerDelivery fast charger, black

- 100 W of power for your smartphone or laptop
- Type-C port or standard USB port for fast charging most smartphones
- Supports both USB PD and QC 3.0 fast charging protocol
- GaN technology enables a more compact energy efficient design



Features

- 4-port 100 W USB fast charger: supports both QC 3.0 and PowerDelivery (PD) specification
- GaN technology: compact design and increased energy efficiency
- Type-C ports support up to 100 W PD, Type-A ports support 30 W QC 3.0
- Intelligent over-current, over-voltage, short circuit and overheat protection
- Practical AC power cord

Packaging

Q'ty in crtn, pcs	48
Crtn volume, CUM	0.057
Crtn weight, kgs	17.29
Individual package size LxWxH:	47x105x140 mm
Carton size LxWxH:	520x335x330 mm
Country of origin	CN
Barcode	8716309133852
Customs code	8504408390

Certificates



Specifications

Input voltage: 110 V 240 V ~, up to 2.0 A
 USB-C1/C2: 5.0V/3.0A, 9.0V/3.0A, 12.0V/3.0 A, 15.0V/3.0A, 20.0V/5.0A (Max. 100W)
 USB-A1/A2: 5.0V/3.0A, 9.0V/3.0A, 12.0V/2.5A (Max. 30W)
 USB-C1+C2: 65W+35W (Max. 100W)
 USB-C1/C2+A1/A2: 70W+30W (Max. 100W)
 USB-A1+USB-A2: 7.5W+7.5W (Max. 15W)
 USB-C1+C2+A1/A2: 45W+35W+18W (Max. 98W)
 USB-C1/C2+A1+A2: 70W+15W (Max. 85W)
 USB-C1+C2+A1+A2: 45W+35W+15W (Max. 95W)
 Standby power consumption: <0.1 W
 Average efficiency: >82.3 %
 Efficiency at 25% load: >83 %
 Efficiency at 100% load: >84.6 %
 Output protection: short circuit, over-voltage, overcharge, overheat

Power cord length: 1.5 m
 Dimensions: 43 mm x 37 mm x 102 mm
 Net weight: 209 g