

TA-UC-2A2C-PD65-01-BK

4-port 65 W GaN USB PowerDelivery fast charger, black

- 65 W of power for your smartphone or laptop
- Type-C port or standard USB port for fast charging most smartphones
- Supports both USB PD and QC 3.0 fast charging protocol
- GaN technology enables a more compact energy efficient design



Features

- 4-port 65 W USB fast charger: supports both QC 3.0 and PowerDelivery (PD) specification
- GaN technology: compact design and increased energy efficiency
- Type-C ports support 65 W PD, Type-A ports support 30 W QC 3.0
- Intelligent over-current, over-voltage, short circuit and overheat protection
- Practical AC power cord

Packaging

Q'ty in crtn, pcs	48
Crtn volume, CUM	0.057
Crtn weight, kgs	14.67
Individual package size LxWxH:	45x50x140 mm
Carton size LxWxH:	520x335x325 mm
Country of origin	CN
Barcode	8716309133784
Customs code	8504408390

Certificates



Specifications

Input voltage: 100 V 240 V ~, up to 1.5 A
 USB-C1/C2: 5.0V / 3.0A, 9.0V / 3.0A, 12.0V / 3.0A, 15.0V / 3.0A, 20.0V / 3.25A (Max. 65W)
 USB-A1/A2: 5.0V / 3.0A, 9.0V / 3.0A, 12.0V / 2.5A, 20.0V / 1.5A (Max. 30W)

USB-C1+C2: 45W + 20W (65W MAX)
 USB-C1+A1/A2: 45W+18W (63W MAX)
 USB-C2+A1/A2: 36W+18W (63W MAX)
 USB-A1+A2: 5.0V / 3.0A (15W MAX)
 USB-C1/C2+(A1+A2): 45W+15W (60W MAX)
 USB-C1+C2+A1/A2: 30W+18W+18W (65W MAX)
 C1+C2+(A1+A2): 30W+18W+15W (63W MAX)
 Standby power consumption: <0.1 W
 Average efficiency: >82.4 %
 Efficiency at 25% load: >83 %
 Efficiency at 100% load: >85 %
 Output protection: short circuit, over-voltage, overcharge, overheat

Power cord length: 1.5 m
 Dimensions: 41 mm x 41 mm x 75 mm
 Net weight: 151 g