

TA-UC-PDQC100LCD-01-BK

4-port 100W GaN USB fast charger, LCD, black

- 100 W of power for your smartphone or laptop
- Type-C port or standard USB port for fast charging most smartphones
- Supports both USB PD and QC 3.0 fast charging protocol
- GaN technology enables a more compact energy efficient design
- Practical LCD display shows charging status



Features

- 4-port 100 W USB fast charger: supports both QC 3.0 and PowerDelivery (PD) specification
- GaN technology: compact design and increased energy efficiency
- Type-C ports support 100 W PD, Type-A ports supports 30 W QC 3.0
- Practical LCD display shows charging status
- Intelligent over-current, over-voltage, short circuit and overheat protection

Packaging

Q'ty in crtn, pcs	48
Crtn volume, CUM	0.041
Crtn weight, kgs	12.09
Individual package size LxWxH:	45x100x110 mm
Carton size LxWxH:	495x305x270 mm
Country of origin	CN
Barcode	8716309133869
Customs code	8504408390

Certificates



Specifications

Input voltage: 100-230 V~ 50/60 Hz, 2.0 A
 Output ports: 3x USB Type-C, 1x USB-Type-A
 USB-C1/C2/C3: 5.0V/3.0A, 9.0V/3.0A, 12.0V/3.0A, 15.0V/3.0A, 20.0V/5.0A (Max. 100W)
 USB-A: 5.0V/3.0A, 9.0V/3.0A, 12.0V/2.5A (Max. 30W)
 USB-C1+USB-C2: 65W+35W (Max. 100W)
 USB-C1+USB-C 3: 65W+35W (Max. 100W)
 USB-C1+USB-A: 65W+30W (Max. 95W)
 USB-C2+USB-C3: 65W+35W (Max. 100W)
 USB-C2+USB-A: 65W+30W (Max. 95W)
 USB-C3+USB-A: 12W+12W (Max. 24W)
 USB-C1+USB-C2+USB-C3: 45W+35W+20W (Max. 100W)
 USB-C1+USB-C2+USB-A: 45W+35W+18W (Max. 98W)
 USB-C1+(USB-C3+USB-A): 65W+24W (Max. 89W)
 USB-C2+(USB-C3+USB-A): 65W+24W (Max. 89W)
 USB-C1+USB-C2+(USB-C3+USB-A): 45W+35W+15W (Max. 95W)
 Standby power consumption: <0.1 W
 Average efficiency: >83.7 %
 Efficiency at 25% load: >80 %
 Efficiency at 100% load: >87.5 %
 Output protection: short circuit, over-voltage, overcharge, overheat

Dimensions: 85 mm x 36 mm x 94 mm
 Net weight: 204 g

System requirements

The fast charging function is only available for devices that support fast charging