

TA-UC-PDQC65L-W-01

2-port 65W GaN USB fast charger, LED, white

- 65 W of power for your smartphone or laptop
- Type-C port or standard USB port for fast charging most smartphones
- Supports both USB PD and QC 3.0 fast charging protocol
- GaN technology enables a more compact energy efficient design
- Practical LED indicator shows charging status



Features

- 2-port 65 W USB fast charger: supports both QC 3.0 and PowerDelivery (PD) specification
- GaN technology: compact design and increased energy efficiency
- Type-C ports support 65 W PD, Type-A port supports 18 W QC 3.0
- Intelligent over-current, over-voltage, short circuit and overheat protection
- Practical LED charging status indicator

Packaging

Q'ty in crtn, pcs	48
Crtn volume, CUM	0.042
Crtn weight, kgs	14.8
Individual package size LxWxH:	45x80x120 mm
Carton size LxWxH:	410x310x330 mm
Country of origin	CN
Barcode	8716309129602
Customs code	8504408390

Certificates



Specifications

Input voltage: 100-240 V~ 50/60Hz, 1.5 A

Output USB-A: 5.0 V/3.0 A, 9.0 V/2.0 A, 12.0 V/1.5 A (max. 18 W)

Output USB-C: 5.0 V/3.0 A, 9.0 V/3.0 A, 12.0 V/3.0 A, 15.0 V/3.0 A, 20.0 V/3.25 A (max. 65 W)

Output A+C: A(5.0 V/2.4 A, 9.0V/2.0 A,12.0 V/1.5 A, 18 W) + C(5.0 V/3.0 A, 9.0 V/3.0 A,12.0 V /3.0 A,15.0 V/3.0 A, 20.0 V/2.25 A, 45 W) (max. 63 W)

Standby power consumption: 0.3 W

Output protection: short circuit, over-voltage, overcharge, overheat

System requirements

iPhone 8 or newer