

TA-UC-AC2PD65LCD-CAR-01

2-port USB car fast charger, Type-C PD, LCD, 65 W, black

PURE POWER

- 65 W of power for your Type-C laptop, smartphone or iPhone
- Faster charging: perfect for short trips and commutes
- Helps to keep your phone battery full while using power-heavy music or navigation apps
- Practical LCD display shows charging status



Features

- 2-port 30 W PowerDelivery (PD) USB Type-C car fast charger
- Type-C port supports 65 W PD, Type-A port supports 18 W QC 3.0
- Supports simultaneous fast charging on both ports
- Practical LCD display shows charging status
- Intelligent over-current, over-voltage and short circuit protection

Packaging

Q'ty in crtn, pcs	96
Crtn volume, CUM	0.08
Crtn weight, kgs	8.16
Individual package size LxWxH:	145x80x45 mm
Carton size LxWxH:	580x410x335 mm
Country of origin	CN
Barcode	8716309129701
Customs code	8504408390

Specifications

Input voltage: 12-24 V ?, max. 7.0 A

Output USB-A: 5.0 V ? 3.0 A, 9.0 V ? 3.0 A, 12.0 V ? 2.5 A (max. 30 W)

Output USB-C: 5.0 V ? 3.0 A, 9.0 V ? 3.0 A, 12.0 V ? 3.0 A, 15.0 V ? 3.0 A, 20.0 V ? 3.25 A (max. 65 W)

Output USB-A+USB-C: 5.0 V ? 3.0 A, 9.0 V ? 2.0 A, 12.0 V ? 1.5 A + 5.0 V ? 3.0 A, 9.0 V ? 3.0 A, 12.0 V ? 3.0 A, 15.0 V ? 3.0 A, 20.0 V ? 2.25 A (max. 45 W + 18 W)

System requirements

12-24 V DC vehicle cigarette lighter socket

iPhone fast charging is only supported on iPhone 8 or newer

Certificates

