

WM-70ST-01

Full-motion TV wall mount, 37"-70"

- Position your screen perfectly
- Lightweight and maneuverable design



Features

- Double-arm full-motion TV wall mount
- Supports most 37" 70" LCD/LED TV's
- VESA compatible, max. 600 mm x 400 mm
- Wall distance 78 400 mm
- Allows up to 120 degrees swivel and 20 degrees tilting
- Practical integrated bubble level for perfect alignment
- Includes all necessary installation materials

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

3
0.0458843
16.44
752x184x91 mm
770x202x295 mm
CN
8716309127837
8302500000

Package contents

Wall mount elements
Installation accessories kit
Installation manual

Specifications

Material: steel, plastic
Surface finish: powder coating
color: black
Fit screen size: 37" ~ 70"
VESA support: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 600 x 400 mm
Weight capacity: 35 kg
Profile: 78 ~ 400 mm
Tilt range: 0 ° ~ -20 °
Swivel range: +60 ° ~ -60 °
Screen level: +3 ° ~ -3 °
Installation: solid wall
Cable management: Yes
Net weight: 4.65 kg
Dimensions: 400 x 635 x 430 mm

Certificates

