

WM-80ST-05

## TV wall mount (full-motion), 37" - 80"

- Position your screen perfectly
- Lightweight and maneuverable design



### Features

- Single-arm full-motion TV wall mount
- Supports most 37" 80" LCD TV's
- VESA compatible, max. 600 mm x 400 mm
- Allows up to 180 degrees swivel and 18 degrees tilting
- Distance to wall: 76 620 mm
- Practical integrated bubble level for perfect alignment
- Includes all necessary installation materials

### Packaging

|                                |                |
|--------------------------------|----------------|
| Q'ty in crtn, pcs              | 2              |
| Crtn volume, CUM               | 0.031941       |
| Crtn weight, kgs               | 15.25          |
| Individual package size LxWxH: | 347x442x85 mm  |
| Carton size LxWxH:             | 455x360x195 mm |
| Country of origin              | CN             |
| Barcode                        | 8716309127806  |
| Customs code                   | 8302500000     |

### Package contents

Wall mount elements  
Installation accessories kit  
Installation manual

### Certificates



### Specifications

Material: steel, plastic ABS  
Surface finish: powder coating  
Color: black  
Fit screen size: 37" 80"  
VESA compatible: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400, 600 x 400 mm  
Weight capacity: 50 kg  
Profile: 76 ~ 620 mm  
Tilt range: +3 ° ~ -15 °  
Swivel range: +90 ° ~ -90 °  
Screen level: +3 ° ~ -3 °  
Installation: solid wall, double stud (406 mm)  
Cable management: yes  
Net weight: 7.3 kg  
Dimensions: 620 x 685 x 425 mm