

WM-80STR-01

Rotating full motion TV wall mount, 40" - 80"

- Position your screen perfectly
- Lightweight and maneuverable design



Features

- Double arm full-motion TV wall mount with rotation function
- Supports most 40" 80" LCD/LED TV's
- VESA compatible, max. 600 mm x 400 mm
- Wall distance 61 506 mm
- Allows up to 100 degrees swivel and 10 degrees tilting
- Max. 90 degrees rotation: allows to position your TV in both portrait and landscape mode
- Practical cable guides on the arms
- Includes all necessary installation materials

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

3
0.04499625
20.94
640x60x345 mm
650x195x355 mm
CN
8716309127370
8302500000

Package contents

Wall mount elements
Installation accessories kit
Installation manual

Specifications

Material: Steel

Screen size: 40 80"

VESA: 100 x 100 600 x 400 mm

Tilt: -3/+7°

Level adjust: ±3°

Swivel: ±50°

Rotation: 90°

Wall distance: 61 506 mm

Weight capacity: 50 kg / 110 lbs

Certificates

