

WM-80ST-02

Full-motion TV wall mount, 37" - 80"

- Position your screen perfectly
- Lightweight and maneuverable design



Features

- Heavy duty steel LCD screen wall mount
- Supports most 37" 80" LCD TV's
- VESA compatible, max. 600 mm x 400 mm
- Allows up to 120 degrees swivel and 20 degrees tilting
- Distance to wall: 58 402 mm
- Includes all necessary installation materials

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

3
0.031304
19
440x300x65 mm
455x320x215 mm
CN
8716309126229
8302500000

Package contents

Wall mount elements
Installation accessories kit
Installation manual

Specifications

Material: steel, plastic
Surface finish: powder coating
Color: fine texture black
Fit screen size: 37"-80"
Vesa compatible: 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400 mm
Weight capacity: 60 kg
Profile: 58~402 mm
Tilt range: +5°~-15°
Swivel range: +60°~-60°
Screen level: +3°~-3°
Installation: solid wall, double stud (406mm)
Cable management: yes
Net weight: 5.77 kg

Certificates

