



FP DB 36



- Canopy
- dimensions H x W x D: 60 x 360 x 245 mm
- Suitable for box wall:
360 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	360 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:	Stainless steel V2A
Surface treatment:	Powder-coated

DIMENSIONS

Height:	60 mm
Width:	360 mm
Depth:	245 mm
Net weight:	1.905 kg

CERTIFICATES

conforming to the standards:

IEC 61439-3

SALES DATA

Product number: 68000174

EAN: 4012591115977

Pack unit: 1

Customs tariff number: 85371098

ETIM class: DYNAMIC: EC000211 - Gland plate for enclosure/cabinet

ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet

ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet

ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet

ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet

ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet

ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

