



FP FG 200



- Flange
- Suitable for box wall:
270 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:
IP degree of protection:
Suitable for box wall:

Fastening material
IP65
270 mm

AMBIENT CONDITIONS

Application area:
Maximum ambient temperature 24 h:
Ambient temperature:
Relative humidity:

Indoor installation
35 °C
-5 °C up to +40 °C
≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height: 50 mm
Width: 270 mm
Net weight: 0.404 kg
Mounting height: 92 mm
Mounting width: 240 mm

CERTIFICATES

conforming to the standards: IEC 61439-3

SALES DATA

Product number:	68000067
EAN:	4012591104889
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

