



FP FG 222



- Flange
- sealing range: 17 x 6 mm - 13 mm
1 x 11 mm - 30 mm
2 x 9 mm - 17 mm
2 x 8 mm - 23 mm
- Suitable for box wall:
270 mm

CONNECTION DATA

CABLE ENTRIES

Cable entries:

Number of cable entries	Type of cable entry	Sealing range of the cable entry	Location of cable entry
17	elastic membranes	6 mm - 13 mm	wall
1	elastic membranes	11 mm - 30 mm	wall
2	elastic membranes	9 mm - 17 mm	wall
2	elastic membranes	8 mm - 23 mm	wall

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	270 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	70 mm
Width:	270 mm
Net weight:	0.483 kg

CERTIFICATES

conforming to the standards:	IEC 61439-3
------------------------------	-------------

SALES DATA

Product number:	68000068
EAN:	4012591104902
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

