



FP FG 300



- Flange
- Suitable for box wall:
360 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	360 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	50 mm
Width:	360 mm
Net weight:	0.5374 kg
Mounting height:	92 mm
Mounting width:	330 mm

CERTIFICATES

conforming to the standards:	IEC 61439-3
------------------------------	-------------

SALES DATA

Product number:	68000105
EAN:	4012591105541
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

