



KST 82



CONNECTION DATA

MECHANICAL PROPERTIES

IP degree of protection:	IP54
Sealing range of the cable entry:	30 mm - 72 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-25 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:	TPE
Glow wire test according to IEC 60695-2-11:	750 °C
Temperature resistance:	-25 °C up to +100 °C
Halogen-free:	Yes
Silicone-free:	Yes

DIMENSIONS

Net weight: 0.134 kg

SALES DATA

Product number: 36001022
EAN: 4012591117599
Pack unit: 1
Customs tariff number: 85369010
ETIM class: DYNAMIC: EC000451 - Cable plug sealing clamp
ETIM-8.0: EC000451 - Cable plug sealing clamp
ETIM-7.0: EC000451 - Cable plug sealing clamp
ETIM-6.0: EC000451 - Cable plug sealing clamp
ETIM-5.0: EC000451 - Cable plug sealing clamp
ETIM-4.0: EC000451 - Cable plug sealing clamp