



Mi 0801



- Empty box
- dimensions H x W x D: 600 x 600 x 170 mm

ELECTRICAL PROPERTIES

Rated insulation voltage:

Rated insulation voltage	Voltage type
$U_i = 690\text{ V}$	a.c.
$U_i = 1000\text{ V}$	d.c.

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Protection cover according to DIN EN 61439 via lid	
Type of lid fastening:	Tool operation
Can be combined:	Yes
IP degree of protection:	IP65
Impact strength:	IK08

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-25 °C up to +70 °C

MATERIAL PROPERTIES

Material:	Polycarbonate
Glow wire test according to IEC 60695-2-11:	960 °C
UV-beständig nach DIN EN 61439-1:	Yes
Halogen-free:	Yes
Silicone-free:	Yes

DIMENSIONS

Height:	600 mm
Width:	600 mm
Depth:	170 mm
Net weight:	6.359 kg
Mounting height:	575 mm
Mounting width:	575 mm

Mounting depth:

Equipping	Depth
without	150 mm
Mounting plate	146 mm
DIN rail	135 mm

COLOURS

Colour of the lid:	Grey
Bottom part colour:	Grey

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:2000013

EAN:4012591650133

Pack unit:1

Customs tariff number:85371098

ETIM class:

DYNAMIC: EC000058 - Empty cabinet

ETIM-9.0: EC000058 - Empty cabinet

ETIM-8.0: EC000058 - Empty cabinet

ETIM-7.0: EC000058 - Empty cabinet

ETIM-6.0: EC000058 - Empty cabinet

ETIM-5.0: EC000058 - Empty cabinet

ETIM-4.0: EC000058 - Empty cabinet

NOTE

Note on the product:

- Cable entry only possible via flanges

Rated loading factors

Power dissipation capability:

power dissipation capability Pde	Temperature difference
P _{de} = 3.3 W	1 K

DRAWINGS



