



Mi 0601



- Empty box
- dimensions H x W x D: 450 x 600 x 170 mm

ELECTRICAL PROPERTIES

Rated insulation voltage:

Rated insulation voltage	Voltage type
$U_i = 690 \text{ V}$	a.c.
$U_i = 1000 \text{ V}$	d.c.

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Protection cover according to DIN EN 61439 via lid

Type of lid fastening: Tool operation

Can be combined: Yes

IP degree of protection: IP65

Impact strength: IK08

AMBIENT CONDITIONS

Application area: Indoor installation

Maximum ambient temperature 24 h: 35 °C

Ambient temperature: -25 °C up to +70 °C

MATERIAL PROPERTIES

Material: Polycarbonate
Glow wire test according to IEC 60695-2-11: 960 °C
UV-beständig nach DIN EN 61439-1: Yes
Halogen-free: Yes
Silicone-free: Yes

DIMENSIONS

Height: 450 mm
Width: 600 mm
Depth: 170 mm
Net weight: 5.335 kg
Mounting height: 425 mm
Mounting width: 575 mm

Mounting depth:

Equipping	Depth
without	150 mm
Mounting plate	146 mm
DIN rail	135 mm

COLOURS

Colour of the lid: Grey
Bottom part colour: Grey

CERTIFICATES

conforming to the standards: IEC 61439-2

SALES DATA

Product number: 20001318
EAN: 4012591120858
Pack unit: 1

Customs tariff number:85371098

ETIM class: DYNAMIC: EC000058 - Empty cabinet
ETIM-9.0: EC000058 - Empty cabinet
ETIM-8.0: EC000058 - Empty cabinet
ETIM-7.0: EC000058 - Empty cabinet
ETIM-6.0: EC000058 - Empty cabinet
ETIM-5.0: EC000058 - Empty cabinet
ETIM-4.0: EC000058 - Empty cabinet

Rated loading factors

Power dissipation capability:

power dissipation capability Pde	Temperature difference
P _{de} = 2.6 W	1 K

DRAWINGS



