



Mi 9300



- Empty box
- dimensions H x W x D: 450 x 315 x 170 mm
- with hinged lid, hinge, external

ELECTRICAL PROPERTIES

Rated insulation voltage:

Rated insulation voltage	Voltage type
$U_i = 690\text{ V}$	a.c.
$U_i = 1000\text{ V}$	d.c.

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Protection cover according to DIN EN 61439 via lid
Type of lid fastening: Tool operation
Can be combined: Yes
IP degree of protection: IP65

Impact strength:

IK08

AMBIENT CONDITIONS

Application area:

Indoor installation

Maximum ambient temperature 24 h:

35 °C

Ambient temperature:

-25 °C up to +70 °C

MATERIAL PROPERTIES

Material:

Polycarbonate

Under the influence of acid (10%), the hinges may become discoloured and brittle. The functionality is not limited.

Glow wire test according to IEC

60695-2-11:

960 °C

UV-beständig nach DIN EN 61439-1:

Yes

Halogen-free:

Yes

Silicone-free:

Yes

DIMENSIONS

Height:

450 mm

Width:

315 mm

Depth:

170 mm

Net weight:

2.786 kg

Mounting height:

425 mm

Mounting width:

275 mm

Mounting depth:

Equipping	Depth
without	150 mm
Mounting plate	146 mm
DIN rail	135 mm

COLOURS

Colour of the lid:

Transparent

Bottom part colour:

Grey

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:	20001049
EAN:	4012591111047
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000058 - Empty cabinet ETIM-9.0: EC000058 - Empty cabinet ETIM-8.0: EC000058 - Empty cabinet ETIM-7.0: EC000058 - Empty cabinet ETIM-6.0: EC000058 - Empty cabinet ETIM-5.0: EC000058 - Empty cabinet ETIM-4.0: EC000058 - Empty cabinet

NOTE

Note on the product:

- trilaterally combinable
- lid hinges attached

DRAWINGS



