



Mi BS 6

- Cover

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:

Fastening material

AMBIENT CONDITIONS

Application area:

Indoor installation

Maximum ambient temperature 24 h:

35 °C

Ambient temperature:

-5 °C up to +40 °C

Relative humidity:

≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:

46 mm

Width:

108 mm

Depth:

39 mm

Net weight:

0.027 kg

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:	20000073
EAN:	4012591650638
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC002498 - Accessories/spare parts for low-voltage switch technology ETIM-8.0: EC002498 - Accessories/spare parts for low-voltage switch technology ETIM-7.0: EC002498 - Accessories/spare parts for low-voltage switch technology ETIM-6.0: EC002498 - Accessories/spare parts for low-voltage switch technology ETIM-5.0: EC002498 - Accessories/spare parts for low-voltage switch technology ETIM-4.0: EC002498 - Accessories/spare parts for low-voltage switch technology

NOTE

Suitable for:	Hinged flap
---------------	-------------

DRAWINGS

