



Mi CB 10



- Connection Box

ELECTRICAL PROPERTIES

Protection class: II

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	300 mm
Steckdose drehbar:	No
Position des Anbaus:	Bottom, laterally

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material: Polycarbonate

DIMENSIONS

Height:	150 mm
Width:	300 mm
Depth:	170 mm
Net weight:	0.966 kg
Mounting height:	125 mm
Mounting width:	240 mm

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	20001071
EAN:	4012591111610
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000784 - Desk system (enclosure/cabinet) ETIM-9.0: EC000784 - Desk system (enclosure/cabinet) ETIM-8.0: EC000784 - Desk system (enclosure/cabinet) ETIM-7.0: EC000784 - Desk system (enclosure/cabinet) ETIM-6.0: EC000784 - Desk system (enclosure/cabinet) ETIM-5.0: EC000784 - Desk system (enclosure/cabinet) ETIM-4.0: EC000784 - Desk system (enclosure/cabinet)

NOTE

Note on the product:

- For the installation of devices that have to be operated from the outside.

DRAWINGS

