



Mi DB 01

- Canopy
- end bracket for canopy Mi DB xx and FP DB xx
- dimensions H x W x D: x 74 x 245 mm
- set with 2 pieces

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:

Fastening material

AMBIENT CONDITIONS

Application area:

Indoor installation

Maximum ambient temperature 24 h:

35 °C

Ambient temperature:

-5 °C up to +40 °C

Relative humidity:

≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:

Stainless steel V2A

Surface treatment:

Powder-coated

DIMENSIONS

Width:

74 mm

Depth:

245 mm

Net weight:

0.884 kg

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:	20001249
EAN:	4012591115984
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

