



Mi FM 32



- Flange
- knockouts: 1 x M25, M32, M40
8 x M25, M32
- Suitable for box wall:
300 mm

CONNECTION DATA

CABLE ENTRIES

Cable entries:

Number of cable entries	Type of cable entry	Size of the metric knockouts	Location of cable entry
1	metric knockouts	M25, M32, M40	wall
8	metric knockouts	M25, M32	wall

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	300 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	25 mm
Width:	300 mm
Depth:	100 mm
Net weight:	0.193 kg

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	2000130
EAN:	4012591651307
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

