



Mi FM 50



- Flange
- knockouts: 2 x M20  
4 x M32, M40, M50
- Suitable for box wall:  
300 mm

CONNECTION DATA

CABLE ENTRIES

Cable entries:

| Number of cable entries | Type of cable entry | Size of the metric knockouts | Location of cable entry |
|-------------------------|---------------------|------------------------------|-------------------------|
| 2                       | metric knockouts    | M20                          | wall                    |
| 4                       | metric knockouts    | M32, M40, M50                | wall                    |

MECHANICAL PROPERTIES

|                          |                    |
|--------------------------|--------------------|
| Delivered accessories:   | Fastening material |
| IP degree of protection: | IP65               |
| Suitable for box wall:   | 300 mm             |

AMBIENT CONDITIONS

|                                   |                                   |
|-----------------------------------|-----------------------------------|
| Application area:                 | Indoor installation               |
| Maximum ambient temperature 24 h: | 35 °C                             |
| Ambient temperature:              | -5 °C up to +40 °C                |
| Relative humidity:                | ≤ 50 % at 40 °C, ≤ 100 % at 25 °C |

## DIMENSIONS

|             |          |
|-------------|----------|
| Height:     | 25 mm    |
| Width:      | 300 mm   |
| Depth:      | 100 mm   |
| Net weight: | 0.191 kg |

## CERTIFICATES

|                              |             |
|------------------------------|-------------|
| conforming to the standards: | IEC 61439-2 |
|------------------------------|-------------|

## SALES DATA

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                   |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product number:        | 2000132                                                                                                                                                                                                                                                                                                                                                                                                           |
| EAN:                   | 4012591651321                                                                                                                                                                                                                                                                                                                                                                                                     |
| Pack unit:             | 1                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Customs tariff number: | 85371098                                                                                                                                                                                                                                                                                                                                                                                                          |
| ETIM class:            | DYNAMIC: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet<br>ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet |

## DRAWINGS

