



Mi FM 63



- Flange
- knockouts: 3 x M40, M50, M63
- Suitable for box wall:
300 mm

CONNECTION DATA

CABLE ENTRIES

Cable entries:

Number of cable entries	Type of cable entry	Size of the metric knockouts	Location of cable entry
3	metric knockouts	M40, M50, M63	wall

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	300 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	80 mm
Width:	300 mm
Depth:	100 mm
Net weight:	0.323 kg

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	2000133
EAN:	4012591651338
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

NOTE

Note on the product:	• with additional manoeuvring space
----------------------	---

DRAWINGS

