



Mi DB 15



- Canopy
- dimensions H x W x D: 60 x 150 x 245 mm
- Suitable for box wall:
150 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP65
Suitable for box wall:	150 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:	Stainless steel V2A
Surface treatment:	Powder-coated

DIMENSIONS

Height:	60 mm
Width:	150 mm
Depth:	245 mm
Net weight:	1.011 kg

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:	20001226
EAN:	4012591115991
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

