



Mi FP 82

IP
54

- Flange
- sealing range: 2 x 30 mm - 72 mm
- Suitable for box wall:
300 mm

CONNECTION DATA

CABLE ENTRIES

Cable entries:

Number of cable entries	Type of cable entry	Sealing range of the cable entry	Location of cable entry
2	Insert	30 mm - 72 mm	wall

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP54
Suitable for box wall:	300 mm

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	135 mm
Width:	300 mm
Depth:	100 mm
Net weight:	0.976 kg

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	2000319
EAN:	4012591653196
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

NOTE

Note on the product:	• Degree of protection IP 54 only with additional strain and pressure relief
----------------------	--

DRAWINGS

