



Mi KL 12



- Hinged flap

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:

IP degree of protection:

Sealable without accessories:

With hinged flap:

Fastening material, drilling and sawing template

IP65

Yes

Lid sealable without further accessories

Yes

AMBIENT CONDITIONS

Application area:

Maximum ambient temperature 24 h:

Ambient temperature:

Relative humidity:

Indoor installation

35 °C

-5 °C up to +40 °C

≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:

Width:

Depth:

Net weight:

112 mm

249 mm

20 mm

0.145 kg

CERTIFICATES

conforming to the standards:

IEC 61439-2

SALES DATA

Product number:	2000059
EAN:	4012591650591
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC002527 - Window (enclosure/cabinet) ETIM-4.0: EC002527 - Window (enclosure/cabinet) ETIM-5.0: EC002527 - Window (enclosure/cabinet) ETIM-6.0: EC002527 - Window (enclosure/cabinet) ETIM-7.0: EC002527 - Window (enclosure/cabinet)

NOTE

Note on the product:

- Hinged flap lockable with accessories

DRAWINGS

