



Mi FP 20



- Flange
- Suitable for box wall:
300 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:
IP degree of protection:
Suitable for box wall:

Fastening material
IP65
300 mm

AMBIENT CONDITIONS

Application area:
Maximum ambient temperature 24 h:
Ambient temperature:
Relative humidity:

Indoor installation
35 °C
-5 °C up to +40 °C
≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height:	25 mm
Width:	300 mm
Depth:	100 mm
Net weight:	0.206 kg
Mounting height:	88 mm
Mounting width:	215 mm

CERTIFICATES

conforming to the standards: IEC 61439-2

SALES DATA

Product number:	2000313
EAN:	4012591653134
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000211 - Gland plate for enclosure/cabinet ETIM-9.0: EC000211 - Gland plate for enclosure/cabinet ETIM-8.0: EC000211 - Gland plate for enclosure/cabinet ETIM-7.0: EC000211 - Gland plate for enclosure/cabinet ETIM-6.0: EC000211 - Gland plate for enclosure/cabinet ETIM-5.0: EC000211 - Gland plate for enclosure/cabinet ETIM-4.0: EC000211 - Gland plate for enclosure/cabinet

DRAWINGS

