



Mi MP 4

- Mounting plate
- dimensions H x W x D: 565 x 265 x 4 mm

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:
Suitable for box size:

Fastening material
4, 6, 8

AMBIENT CONDITIONS

Application area:
Maximum ambient temperature 24 h:
Ambient temperature:
Relative humidity:

Indoor installation
35 °C
-5 °C up to +40 °C
≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:	Hard paper, coated
Temperature resistance:	-40 °C up to +120 °C
Surface treatment:	Coated

DIMENSIONS

Height:	565 mm
Width:	265 mm
Depth:	4 mm
Net weight:	0.854 kg
Material thickness:	4 mm

CERTIFICATES

conforming to the standards:	IEC 61439-2
------------------------------	-------------

SALES DATA

Product number:	2000019
EAN:	4012591650195
Pack unit:	1
Customs tariff number:	85371098
ETIM class:	DYNAMIC: EC000213 - Mounting plate for distribution board ETIM-9.0: EC000213 - Mounting plate for distribution board ETIM-8.0: EC000213 - Mounting plate for distribution board ETIM-7.0: EC000213 - Mounting plate for distribution board ETIM-6.0: EC000213 - Mounting plate for distribution board ETIM-5.0: EC000213 - Mounting plate for distribution board ETIM-4.0: EC000213 - Mounting plate for distribution board

DRAWINGS

