




SECTION A-A


MATERIAL:

Insulator : Hi-temp PPS,UL 94V-0,Color:Brown
Contact material : phosphor bronze
Contact plated : Tin plated over nickel

SPECIFICATIONS:

Temperature range : -50°C to 105°C
Current Rating : 1 AMP
Capacitance : 1.0 Picoforads (Max)
Contact Resistance : 30 Milliohms (Max)
Insulation Resistance : 1000 Megohmx (Max)
Withstanding Voltage: AC 600 Vrms
Package : TUBE = Tube

NO OF CONTACTS	A±0.2	B±0.2	C±0.1	D±0.1	E±0.2
20	15.66	15.66	5.08	5.08	17.28
28	18.20	18.20	7.62	7.62	20.87
32	18.20	20.74	7.62	10.16	22.60
44	23.28	23.28	12.70	12.70	28.30
52	25.82	25.82	15.24	15.24	31.65
68	30.90	30.90	20.32	20.32	38.83
84	35.98	35.98	25.40	25.40	46.00



P.C.B LAYOUT

RoHS
Compliant

HSM 玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

APPD.
核准



TOLERANCE
LINEAR

PART NAME 品名

DWG.
製圖

SCALE
比例

SCALE
比例

PLCC SOCKET SMT TYPE 1.27mm XXP
W/O POLARIZATION PEG
TUBE PACKING TIN PLATING
BROWN COLOR ROHS

DATE 制表日

UNIT
單位

SIZE.
紙張尺寸

PART NO.

2023/08/10

PAGE
張數

REV.
版次

料號 C0100-XXNTTN00R