



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 12 mm, No
Order No.	0282900000
Type	H10,0/12
GTIN (EAN)	4008190075972
Qty.	500 ST
Packaging	loose

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E499744

Dimensions and weights

Net weight 0.29 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	4.5 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	5.8 mm	L1 in mm	12.00 mm
Wire connection cross section AWG, max.	AWG 8	Stripping length	12 mm
Conductor cross-section	10 mm ²		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 9.0	27-40-02-01
ECLASS 9.1	27-40-02-01	ECLASS 10.0	27-40-02-01
ECLASS 11.0	27-40-02-01	ECLASS 12.0	27-40-02-01
ECLASS 13.0	27-40-02-01	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

